

Solid Cable Management Raceway with Cover, 1-1/2"(38mm)W x 5/8"(16mm)H - 6.5ft(2m) length, Single Channel PVC Network/Power Cord Hider/Wall Wire Duct, Max 30 Cables, UL Listed - TAA

Product ID: CBMWD3816



This 6.5 ft. (2 m) cable management raceway neatly routes cables in your office or server room, while also concealing them to create a tidy and professional look.

This cable management raceway protects cables from damage while neatly routing them in your office or server room. The raceway is 0.6 in. (16 mm) x 1.5 in. (38 mm).

Made from self extinguishing PVC, that's sturdy and warp proof this network/power cable hider/concealer is M1 Rating NF fire resistant with a 186F (86C) Vicat softening point and are UL/94V-0 Rated.

The cable raceway can be mounting by simply drilling holes through housing and into any surface, or double sided tape can used to secure the raceway (screws and tape not included).

To combine and route this cable management raceway and cap off the ends, StarTech.com offers a wide selection raceway accessories.

The Coupler (CBMWD3816C) (20-Pack), joins two raceways together and extends the length of your raceway.

The End Piece (CBMWD3816E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMWD3816I) (20-Pack), joins two raceways together inside of corners at a 90 degree angle.

The Outside Elbow (CBMWD3816O) (20-Pack), joins two raceways together around corners at a 90 degree angle.

The T Connector (CBMWD3816T) (20 Pack), joins three raceways together in a T-bar.

Certifications, Reports and Compatibility



Applications

- Protects cables from damage while neatly routing them in your office or server room

Features

- **PROFESSIONALLY ORGANIZE & ROUTE CABLES:** Cable management raceway protects 12-30 cables from damage/debris w/closed design & route them in office/server room install by drilling holes/double sided tape
- **INDUSTRIAL STRENGTH:** Sturdy warp-proof, self extinguishing PVC, solid network/power cable hider/concealer is M1 Rating NF fire resistant w/186F Vicat softening point; UL/94V-0 Rated; UL/CSA approved
- **RACEWAY ACCESSORIES:** Coupler (CBMWD3816C), End Piece (CBMWD3816E), Inside Elbow (CBMWD3816I), Outside Elbow (CBMWD3816O), T Connector (CBMWD3816T); sold separately
- **TECHNICAL SPECIFICATIONS:** Length: 6.5ft (2m) Height: 0.6" (16mm) Width: 1.5" (38mm) Max Cable Capacity: 12-30 (subject to thickness) Single Channel Vicat Softening Point: 186F/86C Gray RoHS
- **STARTECH.COM ADVANTAGE:** IT professional's choice for over 30 years; This surface mount cord kit/ single channel wiring duct system is backed for 2 years by StarTech.com, including free 24/5 tech support

Physical Characteristics

Warranty	2 Years
Color	Gray
Material	PVC
Product Length	1.5 in [3.8 cm]
Product Width	78.7 in [200.0 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	15.0 oz [424.0 g]

Packaging Information

Package Quantity	1
Package Length	1.5 in [3.8 cm]

Package Width	6.6 ft [2.0 m]
Package Height	0.6 in [1.6 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - Raceway
---------------------	-------------

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***