

## Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Patch cable, degree of protection: IP20, cable length: 20 m, CAT6A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

### Your advantages

- ✓
- ✓
- ✓
- ✓
- ✓
- ✓



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 321864
GTIN	4063151321864
Weight per Piece (excluding packing)	959.000 g
Custom tariff number	85444290
Sales Key	ABNAAN

### Technical data

#### Dimensions

Length of cable	20.00 m
-----------------	---------

#### General data

Overvoltage category	I
Degree of pollution	2
Locking type	Locking clips
Rated voltage (III/2)	72 V
Number of positions	8

# Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

## Technical data

### General data

Transmission characteristics (category)	CAT6 <sub>A</sub>
---	-------------------

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Degree of protection	IP20

### Characteristics head 1

Color	gray
Insertion/withdrawal cycles	≥ 750
Ambient temperature (operation)	-20 °C ... 80 °C

### Characteristics head 2

Color	gray
Insertion/withdrawal cycles	≥ 750
Ambient temperature (operation)	-20 °C ... 80 °C

### Cable

Type of cable	Round cable
Cable structure	4x2x26/7, S/FTP
External sheath, color	gray
External cable diameter D	6.2 mm (0.3 mm)
Smallest bending radius, movable installation	50 mm
Outer sheath, material	LSZH
Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	1500 V DC
Flame resistance	IEC 60332-1-2
Halogen-free	complying with IEC 60754-1/2
Ambient temperature (storage/transport)	0 °C ... 40 °C
Shielded	yes
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	7-wire

### Standards and Regulations

Flame resistance	IEC 60332-1-2
Halogen-free	complying with IEC 60754-1/2

### Classifications

#### eCl@ss

eCl@ss 11.0	27440390
eCl@ss 9.0	27440107

#### ETIM

ETIM 7.0	EC001121
----------	----------

# Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / EAC / cULus Listed

---

#### Ex Approvals

---

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 335024
-----------	--	---	---------------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 335024
------------	--	---	---------------

EAC			19060508
-----	--	--	----------

cULus Listed			
--------------	--	--	--

## Accessories

### Accessories

#### Data cable preassembled

#### Patch cable - NBC-R4OC/0,3-BC5/R4OC - 1227558



Patch cable, degree of protection: IP20, cable length: 0.3 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

## Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

### Accessories

Patch cable - NBC-R4OC/0,5-BC5/R4OC - 1227559



Patch cable, degree of protection: IP20, cable length: 0.5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/1,0-BC5/R4OC - 1227560



Patch cable, degree of protection: IP20, cable length: 1 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/1,5-BC5/R4OC - 1227561



Patch cable, degree of protection: IP20, cable length: 1.5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/2,0-BC5/R4OC - 1227562



Patch cable, degree of protection: IP20, cable length: 2 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/3,0-BC5/R4OC - 1227563



Patch cable, degree of protection: IP20, cable length: 3 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

### Accessories

Patch cable - NBC-R4OC/5,0-BC5/R4OC - 1227564



Patch cable, degree of protection: IP20, cable length: 5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/7,5-BC5/R4OC - 1227565



Patch cable, degree of protection: IP20, cable length: 7.5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/0,3-BC6A/R4OC - 1227572



Patch cable, degree of protection: IP20, cable length: 0.3 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/0,5-BC6A/R4OC - 1227573



Patch cable, degree of protection: IP20, cable length: 0.5 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/1,0-BC6A/R4OC - 1227575



Patch cable, degree of protection: IP20, cable length: 1 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

### Accessories

Patch cable - NBC-R4OC/1,5-BC6A/R4OC - 1227578



Patch cable, degree of protection: IP20, cable length: 1.5 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/2,0-BC6A/R4OC - 1227580



Patch cable, degree of protection: IP20, cable length: 2 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/3,0-BC6A/R4OC - 1227581



Patch cable, degree of protection: IP20, cable length: 3 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/5,0-BC6A/R4OC - 1227583



Patch cable, degree of protection: IP20, cable length: 5 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/7,5-BC6A/R4OC - 1227585



Patch cable, degree of protection: IP20, cable length: 7.5 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593

### Accessories

Patch cable - NBC-R4OC/10,0-BC6A/R4OC - 1227588



Patch cable, degree of protection: IP20, cable length: 10 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/12,5-BC6A/R4OC - 1227590



Patch cable, degree of protection: IP20, cable length: 12.5 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/15,0-BC6A/R4OC - 1227591



Patch cable, degree of protection: IP20, cable length: 15 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593



Patch cable, degree of protection: IP20, cable length: 20 m, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---