



Filter mat, Extract: W: 116 mm, H: 116 mm, IP55

Model		
product brand name		SIVACON
product designation		filter mat
type of ventilation		ventilation
fan design withdrawable fan		No
design of the product EMC version		No
General technical data		
cutout width		116 mm
cutout height		116 mm
Protection class		
protection class IP		IP55
Product details		
product component fan		No
Mechanical Design		
height		116 mm
width		116 mm
fastening method		Other
fastening method		
• 19-inch installation		No
• wall mounting		No
net weight		0.1 kg
material		plastic
ambient temperature during operation		
• minimum		-10 °C
• maximum		55 °C
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6000-0CF25>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6000-0CF25>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6000-0CF25

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

