

MATERIAL:
 HOUSING MATERIAL: PBT
 FLAMABILITY RATING: UL94-V0
 COLOR: RED
 CONTACT MATERIAL: PHOSPHOR BRONZE
 CONTACT TYPE: STAMPED
 CONTACT PLATING: MATT TIN OVER NICKEL
 QUALITY CLASS: 25 MATING CYCLES
 PITCH: 2.54 MM PER ROW

ENVIRONMENTAL:
 OPERATING TEMPERATURE: -40°C UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL:
 CURRENT RATING: 1.5 A PER PIN (PCB PIN)
 WORKING VOLTAGE: 100VAC
 INSULATION RESISTANCE: >1000MOHM
 DIELECTRIC WITHSTANDING VOLT.: 500VAC/MN
 CONTACT RESISTANCE: 10mOHM MAX



STANDARD
 RoHS CERTIFIED: E323964 / MOD. NUMBER 69035710xx7x

SOLDERING:
 WAVE PROCESS ONLY

DIMENSION:
 DIM.A= 1.27 x No. of Spaces
 DIM.B= DIM.A + 3.3
 DIM.C= DIM.A + 2.1

AVAILABLE
 xx : 4 TO 26 CIRCUITS

PACKAGING:
 x = 2 TUBE

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	
G						
F						
E	27-MAY-11	PCK&DESCRIPTION	GG			
D	07-APR-10	PINNING	JP			
				APPROVAL: RJ	UNIT: MM SCALE: SHEET: 1/1 DRAW: EAGER	DESCRIPTION: MM MALE CONNECTOR WITHOUT LATCH AND WITH POLARIZATION WERI PART NO: 690 357 10 xx 7 x
C	09-MAR-10	STANDARD	JP			
B	27-NOV-07	MODIFICATIONS	EC			
A	03-NOV-06	PDF	JP			
REV	DATE	FILE	BY			
						SIZE A4