

M18 FID2-0X | M18 FUEL™ 1/4" Hex impact driver



- Higher power efficiency under load - outstanding torque of 226 Nm
- Faster driving speed vs. previous model - up to 3600 rpm and 4300 ipm
- Extremely compact design - total length of just 117 mm for access into tight spaces
- DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility
- Mode 1 for precision work
- Mode 2 helps prevent damage to fasteners and material
- Mode 3 delivers maximum performance for the toughest applications

No load speed (rpm) 1900/2800/3600/0-3600

Impact rate (ipm) 1200/3400/4300/0-4300

Tool reception 1/4" Hex

Max. torque (Nm) 119/176/226/0-226

Kit included No batteries supplied, No charger supplied, HD Box

Article Number 4933464087