

6.02153.50 BSZ 12

12 Volt Cordless Drill / Screwdriver BSZ 12

- Variospeed (V) electronics
- 20-level adjustable torque, plus drilling level
- Quick stop
- Quick-action keyless chuck and spindle stop gear for convenient one-hand tool change: Metabo "Quick"
- T-handle for optimum centre of gravity
- Fatigue-free operation due to perfect ergonomics
- Built-in collector fan to prevent overheating
- Bit case for two bits
- Maximum system flexibility through free combination of chargers and battery packs (within a voltage class)
- AIR COOLED technology for speedy charging and long service life
- With "AIR COOLED" charger AC 30, charge time approx. 30 minutes (at 1.4 Ah)

Comparative technical values

| | |
|---------------------------------|--------------------------|
| Type of battery pack | NiCd |
| Battery pack voltage | 12 V |
| Capacity of battery pack | 1,4 Ah |
| Max. torque, soft | 22 Nm |
| Max. torque, hard | 52 Nm |
| Adjustable torque | 1,3 - 6,2 Nm |
| Drill diameter in | |
| - Steel | 10 mm/5 mm |
| - Wood | 25 mm/20 mm |
| No-load speeds | 0 - 400 / 0 - 1.350 /min |
| Drill spindle thread | 1/2" -20 UNF |
| Chuck capacity | 1,5 - 13 mm |
| Weight (including battery pack) | 2 kg |