

Feeler Gauge Foils

Feeler Gauge Spare Blades

- When ordering, please specify blade thickness!



ART N° spring steel	steel thickness up to max. mm / inch	ART N° brass	brass thickness up to max. mm / inch	conical shape	cylindrical shape	length of blade mm
421110	2 / .08	424110	1 / .04	✓	—	100
431150	2 / .08	—	—	—	✓	150
431200	2 / .08	—	—	—	✓	200
431300	2 / .08	—	—	—	✓	300
431500	2 / .08	—	—	—	✓	500

Thickness Gauge Foils

tolerance acc.to T2

- 5 meter, rolled
- for automotive and engine industry and as levelling foil

- hardened spring steel or stainless steel, hard rolled out
- sizes in mm and inch on each blade
- rolled in a rugged plastic box
- From thickness 1.10 mm – 2.00 mm → only available in string of 1 m length
- from 0.65 mm rolled, without box

Other sizes available
on request



T2



ART N° spring steel	ART N° stainless steel	mm / inch	length m	ART N° spring steel	ART N° stainless steel	mm / inch	length m
455001	456001	0.01 / .0004	5	455055	—	0.55 / .022	5
455002	456002	0.02 / .0008	5	455060	—	0.6 / .024	5
455003	456003	0.03 / .0012	5	455065	—	0.65 / .026	5
455004	—	0.04 / .0016	5	455070	—	0.7 / .028	5
455005	456005	0.05 / .002	5	455075	—	0.75 / .03	5
455006	—	0.06 / .0024	5	455080	—	0.8 / .032	5
455007	—	0.07 / .0028	5	455085	—	0.85 / .034	5
455008	—	0.08 / .003	5	455090	—	0.9 / .036	5
455009	—	0.09 / .0035	5	455095	—	0.95 / .038	5
455010	456010	0.1 / .004	5	455100	456100	1 / .04	5
455012	—	0.12 / .005	5	457110	—	1.1	1
455015	456015	0.15 / .006	5	457120	—	1.2	1
455018	—	0.18 / .007	5	457130	—	1.3	1
455020	456020	0.2 / .008	5	457140	—	1.4	1
455025	456025	0.25 / .01	5	457150	—	1.5	1
455030	456030	0.3 / .012	5	457160	—	1.6	1
455035	—	0.35 / .014	5	457170	—	1.7	1
455040	456040	0.4 / .016	5	457180	—	1.8	1
455045	—	0.45 / .018	5	457190	—	1.9	1
455050	456050	0.5 / .02	5	457200	—	2	1

Holder for Feeler Gauge Blades



ART N°

458010



size

125 x 17 mm