

Features

- 3.5mm Pluggable Rising Clamp Terminal Block Female
- 2-12 pole solid Block
- Pluggable male-female connectors
- Closed headers
- Polarised mouldings
- Moulded in green flame retardant PA66
- Professional rising clamp terminals
- 1.0mm² (28-16AWG) solid & stranded cable
- Anti solder wicking
- Captive screws
- Guided pin alignment

RS PRO CTBP92HD Series Pluggable Terminal Block, 10-Contact, 3.5 mm Pitch, 1 Row

RS Stock No: 173-1620



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO CTBP92HD Series Pluggable Terminal Block is a reliable 10-contact male connector designed for secure wire-to-board connections in industrial and electronic applications. Featuring a compact 3.5 mm pitch, screw-clamp wire termination, and a robust polyamide housing, it supports currents up to 10 A and voltages up to 300 V. Its pluggable design enables quick installation and maintenance, making it ideal for control panels, automation equipment, and PCB connectivity applications.

General Specifications

Product Type	Pluggable Terminal Block
Number Of Contacts	10
Housing Material	Polyamide
Connector Gender	Male
Maximum Wire Size mm ²	1mm ²
Minimum Wire Size AWG	16AWG
Maximum Wire Size AWG	28AWG
Orientation	Straight
Colour	Green
Type Of Connection	Screwed
Series	CTBP92HD

Electrical Specifications

Operating Current	10A
Operating Voltage	300V

Pluggable Terminal Blocks



Mechanical Specifications

Corrosion Resistance	Yes / No
Width	11.2mm
Length	35.8mm
Depth	16.2mm
Pitch	3.5mm

Similar Products

Stock No.	Brand	Product Name	Number of Contacts	Current	Voltage
173-1621	RS PRO	RS PRO CTBP92HD Series Pluggable Terminal Block, 12-Contact, 3.5 mm Pitch, 1 Row	12	10A	300V