

Datasheet

RS Pro 3001 Series 5mm Pitch Straight PCB Terminal Block with Cage Clamp Termination, PCB Mount, 4 Way

RS Stock No: **874-5524**



Product Details

RS Pro 4-way straight PCB terminal block comes with cage clamp termination. This vertical mount PCB screwless terminal block has a 5.0 mm pitch, levers and a 300 V 15 A electrical rating. The PCB terminal block features screwless cage clamp terminals that accept a wire size of 28 to 12 AWG and white PA66 housings.

Specifications:

Body Orientation	Straight
Colour	Grey
Current Rating	10 A (UL), 15 A (IEC)
Depth	15 mm
Gender	Female
Length	21 mm
Material	Nylon 66
Mounting Type	PCB
Number of Contacts	4
Number of Rows	1
Pitch	5 mm
Termination Method	Cage Clamp
Type	PCB Terminal Block
Voltage Rating	300 V (UL), 250 V (IEC)
Width	16.3 mm
American Wire Gauge	14 to 26 AWG
Insulation Withstands Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ
Flammability Rating	UL 94 V-0