

Features

- Tempered glass window
- Range 10 bar

Integrated gauge 0-10 Bar

RS Stock No.:

0767790



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A compact pressure gauge with a square dial suitable for air treatment units.
To replace units in the RS PRO range. (see below)
Mounting can be achieved by unscrewing the two screws, (top right and bottom left)
No sealant is required.
The pressure gauge has a neck to dampen pressure vibration.
This improves overall reliability and guarantees longer life.

General Specifications

Mounting Type	Back Entry
Display type	Analogue
Series	EAC-20
Case Material	POM
Window Material	Plastic
Accessory to be used with	2351092, 2351097 2351098, 2351099 2351100, 2351101 2351103, 2351104, 2351105

Pressure Range	0 → 10 bar
Working Pressure	75% of FSV for static pressure; 66% of FSV for pulsating pressure
Maximum Pressure Measurement	10 bar
Minimum Pressure Measurement	0 bar
Connection Size	Integrated
Gauge Outside Diameter	28.4 mm
Minimum Operating Temperature	0°C
Maximum Operating Temperature	+65°C
Calibrated	No

Technical Specifications and Drawings

