



Actual

**Catalog Number:** TY300-50X-100  
**Product ID:** 7TAG054360R0279  
**UPC Number:** 78621023224  
**EAN Number:** 05414363075325  
**Status:** A

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 302.26mm (11.9 Inches), Width of 4.673mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), 100 Pack

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	General Purpose
Width	0.184 in ; 4.674 mm
Length	11.9 in ; 302.26 mm
Thickness	0.049 in ; 1.24 mm
Bundle Diameter	3 in ; 76.2 mm
Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	50 pounds ; 222 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	4.673mm
Length belt/tape/tie	302.26mm
Tie thickness	1.24mm
Max. bundle diameter	76.2mm
Min. holding force	220N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

**Packaging**

Inner Quantity	100
Inner Dimensions (inches)	16x2x6
Outer Quantity	5000
Outer Dimensions (inches)	17x13.5x10.25
Weight Uom	3.75 lbs. per 1000

**For further technical assistance, please contact us...**



860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)