

DWE4559-QS

230 mm 2400W Grinder - Trigger Switch



5035048394922

Product Description:

Disc Ø (mm): 230 Power: 2400W No-load Temperature (RPM): 0-6500 Spindle Thread: M14 Vibration Level (m/s²): 7.0 Switch: Trigger



Product features and benefits:

- Anti-vibration side handle, improves user comfort
- Dust-sealed ball bearings for added durability of the tool Protective guard can be adjusted quickly, without tools
- 3-position side handle for better operating comfort Self-adjusting
- brushes for longer motor life Inductor with connecting wires directly
- from the winding for better tool life Design with the Dust Ejection
- System (DES) to protect the motor from particles and increase service life
-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Indoor/Outer Flange (x1)
- Anti-Vibration Side Handle (x1)
- Tool-Free Protective Guard (x1)
- Service Key (x1)

Specifications techniques :

- Power: 2400 W
- Power supply: 2400 V
- Disc diameter: 230 mm
- Disc diameter: 230 mm

