



PRODUCT-DETAILS

NVNV-M160-5

FTNG STR M16 NW10 PA6/BR 5 IP68 BLK



General Information	
Extended Product Type:	NVNV-M160-5
Product ID:	7TAA292150R0652
EAN:	7630030256660
Catalog Description:	FTNG STR M16 NW10 PA6/BR 5 IP68 BLK
Long Description:	PMAFIX Straight Black Connector with Metric Threads, Connector Material - Polyamide 6, Thread Material - Nickel Plated Brass, Thread Size - M16x1.5, Thread Length - 5, Conduit Size NW - 10
Display Name:	NVNV-M160-5

Eco Transparency	
Environmental Product Declaration - EPD:	9AKK108471A8618

Additional Information	
Product Main Type:	PMA Flexible Cable Protection

Application:	For Use In the Heavy Machine and Railway Vehicle Construction Sectors Where Increased Demands are Made of the System Properties
Product Type:	Connectors-Straight

Ordering

EAN:	7630030256660
UPC:	786209963871

Technical

Number of Batteries:	0
Color:	Black
Material:	Polyamide 6 with Nickel Plated Brass Threads
Size:	NW10 , M16 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
-----------------------	---------------------------

Container Information

Package Level 1 Units:	500 EA
Package Level 1 EAN:	7630030256660
Package Level 1 Height:	200 mm 7.874 in
Package Level 1 Depth / Length:	399.999 mm 15.748 in
Package Level 1 Width:	299.999 mm 11.811 in

Certificates and Declarations

Data Sheet, Technical Information:	NVNV-M160-5
Instructions and Manuals:	NVNV-M160-5
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

