
Features

- 2:1 shrink ratio
- Operating temperature -55°C to 135°C
- Dielectric strength of 20 kV/mm
- Flame retardant (except clear)
- Excellent electrical, chemical, and physical properties
- Available in a wide range of colours

RS PRO PLF 100

RS Stock No.: 0758133, 0731148, 0731149, 0731150, 0731152, 0731153, 0731154, 0731160, 0758134



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro PLF100 provides superior abrasion resistance when compared with that of many flexible, general purpose polyolefin tubings. This 2:1 ratio heat shrinkable sleeving has excellent physical and chemical properties that meet or exceed most of the common industrial and commercial standards.

Approvals

Specifications	UL 224 CSA LR31929 RoHS Compliant VW-1