



ENGLISH

Datasheet

RS Pro – IP65 Non-Corrosive T8 Fluorescent Ceiling Light Single or Twin Batten – (Lamps not included)

110V or 230V

Emergency Option

Configuration	1 x 18w	1 x 36w	1 x 58w	1 x 70w
230V Standard Single	188-4671	188-4673	188-4676	
230V Emergency Single		188-4672	188-4675	188-4677



Configuration	2 x 18w	2 x 36w	2 x 58w	2 x 70w
230V Standard Twin	188-4678	188-4681	188-4682	188-4686
230V Emergency Twin		188-4680	188-4683	188-4685



Configuration	1 x 58w	2 x 58w
110V Standard	188-4674	188-4684



Datasheet

Description	IP65 HF Non-Corrosive T8 Fluorescent Fitting (Lamp not included)							
Models Available	Standard, Emergency & 110V							
Base Finish	Standard and Emergency = Grey Base / 110V version = Yellow Base							
Configuration	1 x 18w	1 x 36w	1 x 58w	1 x 70w	2 x 18w	2 x 36w	2 x 58w	2 x 70w
230V Standard Product Code	188-4671	188-4673	188-4676		188-4678	188-4681	188-4682	188-4686
230V Emergency Product Code		188-4672	188-4675	188-4677		188-4680	188-4683	188-4685
110V Product Code			188-4674				188-4684	
Length (L)	653	1263	1563	1828	653	1263	1563	1828
Width (W)	94	94	94	94	129	129	129	129
Projection (H)	90	90	90	90	90	90	90	90
Fixing Centre (A1)	390	900	1000	1000	390	900	1000	1000
Wattage (W)	18	36	58	70	36	72	116	140
No Clips	6	10	12	14	6	10	12	14
Typical Location	IP65 makes it suitable for Indoor or Outdoor installation - Protection from Dust & water jets							
Tube(s) Required	1x T8 2ft	1x T8 4ft	1x T8 5ft	1x T8 6ft	2x T8 2ft	2x T8 4ft	2x T8 5ft	2x T8 6ft
Country of Origin	China							
Fitting Instructions	Yes							
Pack Includes	Polycarbonate Clips, surface mount fixing brackets & 20mm compression gland							
Internal Electrical Connection	Push Fit terminals for ease of installation & improved reliability							
Warranty	3 Years for main fitting, 12 months for Emergency battery pack							
Materials								
Body	Polycarbonate							
Diffuser	Polycarbonate - Clear Prismatic							
Gear Tray	Pressed Steel - powder coated white							
Gasket	Silicon Rubber							
Class	Class 1 - Must be earthed							
Driver	Included							
CE Mark	Yes							
Dimmable	No							
Batch Coding	Yes							
Manufactured in accordance	BS EN 60598							

