

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Cordless Vacuum Cleaner

GAS 12V Professional

The most powerful and compact cordless dust extractor

The most important data

Battery voltage	12 V
Container volume	0,35 l
Filter surface area	408 cm ²

**Part number:** 0 601 9E3 000**GBP 62.40***[> More product information](#)** Price including VAT*

Technical Data

Battery and power	
Battery voltage	12 V
Performance data	
Container volume	0,35 l
Filter surface area	408 cm ²
Max. volume flow rate (turbine)	15,0 l/sec
Max. vacuum pressure (turbine)	45 mbar
Size and weight	
Length	273,0 mm
Width	77,0 mm
Height	170,0 mm

**Power tools for trade & industry****Advantages**

- Cordless dust extractor for intermediate cleaning and for cleaning on the go
- Powerful and compact – fits into the L-BOXX!
- Can be clicked into L-BOXX, and into GAS 35 and GAS 55 wet/dry dust extractors
- Suitable for vacuuming various types of dirt, e.g. wood, plastic or metal chips
- Ideal for hard-to-reach areas thanks to crevice nozzle
- Comfortable to use thanks to compact size, low weight and ergonomic design

**HEAVY DUTY****Prices / Scope of delivery**

Part number:	0 601 9E3 000
Flat-pleated filter 2 607 432 046	✓
Crevice nozzle (spare part number 1 600 A00 2PP)	✓
Battery and charger not included	✓
Price (Price including VAT)	GBP 62.40