

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	Legamaster			
	Supplier's address.	Public Contact, Kwinkweerd 62, 7240 AC Lochem Lochem Gelder- land, NL			
2.	Model identifier	EXP-6510			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	C			
4.	On mode power demand in SDR	112			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	n.a.			
6.	On mode power demand in HDR, if implemented	n.a.			W
7.	Off mode, power demand, if applicable	0,0			W
8.	Standby mode power demand, if applicable	0,5			W
9.	Networked standby mode power demand, if applic- able	0,0			W
10.	Electronic display category	Monitor			
11.	Size ratio	16	:	9	
12.	Screen resolution	3 840	x	2 160	pixels
13.	Screen diagonal	165,0			cm
14.	Screen diagonal	65			inches
15.	Visible screen area	116,5			dm ²
16.	Panel technology used	LED LCD			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	60			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	-			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the mar- ket)	-			Years
23.	Minimum guaranteed product support	-			Years
	Minimum duration of the general guarantee offered by the supplier	-			Years
24.	Power supply type	Internal			
25.	External power supply (non standardized and included in the product box)				
	<i>i</i>	-			

	<i>ii</i>	Input voltage	-	V
	<i>iii</i>	Output voltage	-	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

EPREL registration number: 1829788 Model placed on the Union market from 15/04/2024.		 https://eprel.ec.europa.eu/qr/1829788
Supplier: Legamaster International BV (Manufacturer)		Website: www.legamaster.com
Customer care service:		
Name: Public Contact		Website: www.legamaster.com
Email: info@legamaster.com		Phone: (+31) (0)573 - 71 30 00
Address: Kwinkweerd 62 7240 AC Lochem Netherlands		