

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC

Collection: Kaptiv

Upper: Breathable Fabric

Insole: Wire Lace System

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10

Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.

Base

Comfort is what has inspired Base Protection since its first day of activity. The company produces safety footwear, combining technology and functional requirements, to respond to professional and more demanding clients.

Standards

EN ISO 20345: 2011 S1P (HRO SRC)



Features

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC**Commodity Code: 6404199000****Test House**

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)

Via Alberto Riva Villasanta, 3

, Italy

Cert No: N° F-113-05202-22

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1004BKB36	Black/Blue	67.0	41.0	36.0	1.1700	0.0989	8052530121788	
B1004BKB37	Black/Blue	67.0	41.0	36.0	1.7900	0.0989	8052530121795	
B1004BKB38	Black/Blue	67.0	41.0	36.0	1.2020	0.0989	8052530121801	
B1004BKB39	Black/Blue	67.0	41.0	36.0	1.2530	0.0989	8052530121818	
B1004BKB40	Black/Blue	67.0	41.0	36.0	1.3400	0.0989	8052530121825	
B1004BKB41	Black/Blue	67.0	41.0	36.0	1.3600	0.0989	8052530121832	
B1004BKB42	Black/Blue	67.0	41.0	36.0	1.4400	0.0989	8052530121849	
B1004BKB43	Black/Blue	67.0	41.0	36.0	1.4700	0.0989	8052530121856	
B1004BKB44	Black/Blue	67.0	41.0	36.0	1.5300	0.0989	8052530121863	
B1004BKB45	Black/Blue	67.0	41.0	36.0	1.5800	0.0989	8052530121870	
B1004BKB46	Black/Blue	67.0	41.0	36.0	1.5950	0.0989	8052530121887	
B1004BKB47	Black/Blue	67.0	41.0	36.0	1.6200	0.0989	8052530121894	
B1004BKB48	Black/Blue	67.0	41.0	36.0	1.6290	0.0989	8052530121900	