

Paddle Mixer LXT®

DUT130

18V • 0 – 1 300 min⁻¹ • 165 mm

Battery-powered brushless mixer for paint, mortar and other such materials

Lightweight, battery-powered mixer with brushless motor for mixing screeds and mortars in max. 30kg batches. Easy to handle and carry within the job site. Maximum blade diameter 120mm. Two speed ranges and stepless adjustment from the operating switch.



Technical specifications

Nominal Battery Voltage	18 V
Brushless Motor	✓
Voltage LXT	✓
No load speed	0 - 350 / 1300 min ⁻¹
Spindle Thread	1/2" / M14
Blade diameter (beater)	165 mm
Sound Pressure Level (L _{pA})	77 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	2,5 - 2,8 kg
Product Dimensions (L x W x H):	320 x 89 x 231 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Product net weight	1,9 kg

User benefits

- Brushless maintenance-free and long-life motor
- Variable 2-speed options allows the user to match speed to application
- Battery cover minimizes the chance that spattered material might adhere to battery
- Variable speed trigger allows operator to adjust speed based on materials or application
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Soft start feature for added motor protection
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

140G50-6

Grip Complete

458814-5

Front Cover

P-22012

Mixing Blade 120 x 590 mm

P-22040

Mixing Blade 135 x 590 mm



194254-0

Keyless chuck 13 mm, 1/2" - 20UNF



831253-8

Tote Bag



P-22028

Mixing Paddle 100 x 590mm



P-22056

Mixing Blade 120 x 590 mm



Other

User manual

Parts drawing