



Operating temperature	-40-105 °C
Connector type	Spliceing connector
Flammability rating (UL94)	V2

## **Dimensions:**

Max. AWG-size	14
Min. AWG-size	20
Nominal cross section (device side)	0.5-2.5 mm <sup>2</sup>
Nominal cross section (installation side)	0.5-2.5 mm <sup>2</sup>
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-2.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.5-4 mm <sup>2</sup>
Width	90 mm
Height	11 mm
Strip length	12 mm
MOQ	10 .
Unit	pck
Nominal cross section	0.5-2.5 mm <sup>2</sup>
Length	18 mm
Nominal voltage	450 V

## **Approvals:**

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

## **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	In compliance
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS

## **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Consumer pack
Search Description	SKV2024ERIK3, ENR2025H, EFO2025H
Alternative SKU	SC-40525-S-PP10

E-no

E1441374

**Logistic information:**

---

<b>Barcode</b>	733117641343
<b>Country of origin</b>	CN
<b>E-no</b>	E1441374
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	10 .
<b>Stock code</b>	SC-4 0525-S-PP10
<b>Taric code</b>	85369010
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.