

Cut-off Saw LXT®

DMC300

18V • 76 mm • 20 000 min⁻¹

Powerful LXT® Cut-off Saw for versatile cutting jobs.

Developed mainly for automotive repair shops, plumbing traders and air conditioning equipment suppliers, and designed to have enough power and compactness for enabling small jobs, such as cutting thin sheet metals, pipes, etc.



LXT **BL** **AFT** 

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	20000 min ⁻¹
Max. Depth of Cut	16 mm
Electronic brake	✓
Bore Size (Arbor Diameter)	10 mm
Disc Diameter	76 mm
Sound Power Level (L _{WA})	99 dB(A)
Sound Pressure Level (L _{pA})	88 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Concrete Cutting	3,0 m/s ²
Vibration Uncertainty (K Factor), Concrete Cutting	1,5 m/s ²

User benefits

- Constant speed control maintains constant speed under load
- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Soft grip handle provides increased comfort on the job
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Lock-off button prevents accidental startup
- Compact and lightweight for single handed operation
- Reversing switch is conveniently located

Link to product - www.makitauk.com



Related products

Optional AC

D-74815-5

Cut-Off Wheel, 76 x 10 mm, 5 pcs



D-77263

Diamond Wheel 76x10mm



Other

User manual

Parts drawing