

M12 FID2-602X | M12 FUEL™ sub compact 1/4" Hex impact driver



- Brushless POWERSTATE™ motor with faster speed in a more compact size of 127mm
- REDLINK PLUS™ intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load
- 4-Mode DRIVE CONTROL allows the user to shift to three different speed and torque settings, as well as a self-tapping mode to maximise application versatility
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability

No load speed (rpm)	0-1300 / 0-2400 / 0-3300 / 0-3300
Tool reception	1/4" Hex
Impact rate (ipm)	0 - 4000
Max Torque (Nm)	147
Weight with battery pack (EPTA) (kg)	1.2 (M12 B6)
Kit included	2 x M12 B6 Battery packs, C12 C Charger, HD Box
Article Number	4933479878