



Product data sheet

Power tools for trade & industry

Cordless Straight Grinder

PRO GGS 18V-23 LC



The cordless straight grinder with corded performance

The most important data

Battery voltage	18.0 V
No-load speed	23,500 rpm
Tool holder	Collet

Part Number 0 601 229 100

Technical data

Technical data

No-load speed	23,500 rpm
Battery voltage	18.0 V
Weight excl. battery	1.4 kg
Tool holder	Collet
Packaging dimensions (width x length x height)	360 x 441 x 155 mm
Weight incl. battery	0 kg

Noise/vibration information

Surface grinding (roughing with grinding tool diameter of 50 mm)

Vibration emission value ah	5.6 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Next level of power – 1,000 W equivalent: Stronger than standard corded straight grinders due to high-power brushless motor
- Best tool control: With Drop & KickBack Control, Brake and also execution with PROtection switch available
- Best convenience: Thanks to preparation for Connectivity and small grip size for easy handling



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

