

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/pc/products/0808642>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 5 mm, Number of individual labels: 10, text field height: 5.15 mm, text field width: 5.15 mm

Your advantages

- Unmarked marking strips can be custom-labeled with a plotter or by hand
- Other pitches available on request
- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0808642
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2112
GTIN	4017918180355
Weight per piece (including packing)	0.61 g
Weight per piece (excluding packing)	0.315 g
Customs tariff number	39269097
Country of origin	DE

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/pc/products/0808642>

Technical data

Product properties

Pitch	5 mm
-------	------

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Slot type	flat

Dimensions

Width	5.15 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	5 mm

Text field

Text field width	5.15 mm
Text field height	5.15 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/pc/products/0808642>

Mounting type	latching
---------------	----------

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat

0808642

<https://www.phoenixcontact.com/pc/products/0808642>

Drawings

Schematic diagram



ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/pc/products/0808642>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/pc/products/0808642>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.005 kg CO2e
---------	---------------

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat

0808642

<https://www.phoenixcontact.com/pc/products/0808642>




Accessories

PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/pc/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.




CMS-P1-PLOTTER - Marking plotter

5144615

<https://www.phoenixcontact.com/pc/products/5144615>

Marking plotter, weight: 8 kg, length: 0.66 m, width: 440 mm, height: 125 mm, color: silver-colored



ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/pc/products/0808642>

STP 4-2 - Marker carriers

0810575

<https://www.phoenixcontact.com/pc/products/0810575>



Marker carriers, snaps into ST 1,5... spring-cage terminal blocks, can be marked with UC-TM 4, UC-TMF 4, UCT-TM 4, UCT-TMF 4, ZB 4, or ZBF 4, gray, unmarked, mounting type: plug in, text field height: 10.5 mm, text field width: 4 mm

STP 4-2-ZB - Marker carriers

3038613

<https://www.phoenixcontact.com/pc/products/3038613>



Marker carriers, snaps into ST 1,5... spring-cage terminal blocks, can be marked with UC-TM 4, UC-TMF 4, UCT-TM 4, UCT-TMF 4, ZB 4, or ZBF 4, gray, unmarked, mounting type: latching, text field height: 10.5 mm, text field width: 4 mm

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com