

## FEATURES

- High Grade Steel
- Two Layer Front Panel
- Powder Coated Enclosure
- Precise Design
- High Quality Manufacturing standard

# RS PRO Ventilated Rackmount Enclosure, 4U, 84 HP, Height 177mm, 425mm Deep

RS Stock No.: 665-7722



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Introducing the RS PRO PF19 Rackmount Enclosures, a high quality and heavy-duty electronic enclosure series, suitable for a wide range of uses. Constructed from a mixture of high grade rolled steel and lightweight aluminium panels, these rackmount enclosures offer a sturdy construction and combined with the tough powder-coated finish, provide long-lasting life of the product even in harsh environments. The enclosures are easy to use and assemble, thanks to the precision workmanship and well-engineered design. In addition to this, the high-quality materials that are used to manufacture this RS PRO enclosure offer a strong and aesthetically-pleasing finished product, suitable for a wide range of applications both at home or in industry.

## General Specifications

<b>Mounting</b>	Rackmount
<b>Rack Units</b>	4U
<b>Material</b>	Steel
<b>Horizontal Pitch</b>	84HP
<b>Ventilated</b>	Yes
<b>Handles</b>	Yes
<b>Colour</b>	Black
<b>For Use With</b>	In outdoor conditions and exposure to the elements
<b>Rack Size</b>	Half Width
<b>Features</b>	The PF19 enclosure range is available in a wide variety of sizes
<b>Sound Proof</b>	No
<b>Fan Included</b>	No

## Mechanical Specifications

<b>Dimension</b>	177mm x 482.6mm x 425mm
<b>Height</b>	177mm
<b>Depth</b>	425mm
<b>Width</b>	482.6mm

## Approvals

<b>Declarations</b>	RoHS Certificate of Compliance
<b>Standards Met</b>	IEC 297 / EIA RS-310 C1977 / DIN 41494 / ASTM D610-01 / ASTM B117

There are 24 different sizes and configurations which are available in :

- Height : 1.5U to 6U (B)
- Width : 482 (A)
- Depth : 90, 245, 335, 425 and 465 (D)

