

Line Trimmer LXT®

DUR193

18V • 7 800 min⁻¹ • 260 mm

Handy and light line trimmer for trimming lawns

A compact and handy line trimmer for trimming and finishing of gardens and other green spaces. This tool, with a cutting width of 260 mm, has a balanced shaft design for added user convenience. Equipped with an adjustable telescopic shaft.



LXT

Technical specifications

Nominal Battery Voltage	18 V
No load speed	7800 min ⁻¹
Cutting width	260 mm
Tool weight with battery	2,3 - 2,6 kg
Nylon line- Diameter	1,65 mm
Sound Power Level (L _{WA})	82 dB(A)
Sound Pressure Level (L _{pA})	73,5 dB(A)
Noise Uncertainty (K Factor)	2,1 dB(A)
Product Dimensions (L x W x H):	1248 - 1436 x 265 x 358 mm
Voltage LXT	✓
Vibration Level, Nyloncord	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Nyloncord	1,5 m/s ²
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Product net weight	1,9 kg

User benefits

- Lightweight for reduced operator fatigue
- Well balanced design with fully adjustable features to suit any operator
- Telescopic shaft for optimum cutting position
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

■ Optional AC

191Y39-5

Spool Assembly Set 1x1.65mm



■ Other

User manual

Parts drawing