



G3NE-220T-US 24VDC

Compact SSR, 20A, 264 VAC max, zero cross over

Specifications

Application	ON/OFF control
Number of phases	1
Mounting method	Screw
Terminal type	Tab terminal
Complete with socket	✗
LED indicator	✗
Rated operational voltage, AC	100-240 V
Operating voltage range, AC	75-264 V
Rated operation current I _e at AC-1	20 A
Supply voltage DC	19.2-28.8 V
Must operate voltage max.	19.2 V
Must release voltage min.	1 V
Maximum operating temperature	80 °C
Minimum operating temperature	-30 °C
Isolation	Phototriac
Switching at zero-crossing	✓

CAD Library



G3NE Solid State Relays Datasheet

EN PDF 362 KB



Industrial Relays Brochure

EN PDF 2.77 MB