

Angular contact ball bearings 7207-B-XL-MP (Series 72..-B)

main dimensions to DIN 628-1, contact angle $\alpha = 40^\circ$

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	35 mm
D	72 mm
B	17 mm
a	31 mm
D ₁	57,64 mm
d ₁	50,17 mm
D _{a max}	65 mm
d _{a min}	42 mm
D _{b max}	67,8 mm
r _{1 min}	0,6 mm
r _{a1 max}	0,6 mm
r _{a max}	1 mm

r_{min}	1,1 mm	
α	40 °	Contact angle
m	0,295 kg	Mass
C_r	28000 N	Basic dynamic load rating, radial
C_{0r}	19000 N	Basic static load rating, radial
C_{ur}	1320 N	Fatigue limit load, radial
n_G	15800 1/min	Limiting speed
n_{9r}	9600 1/min	Reference speed



