



**Part Number :** [1301460129](#)

**Product Description :** Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V

**Series Number :** 130146

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Number :** 60W47



---

## Documents & Resources

### Drawings

[1301460129 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871402

**Agency**

CSA	LR6837
UL	E68122

**Electrical**

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

**Physical**

Cord Type	N/A
Flange	No

Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No
Net Weight	12.440/g
Poles	2-pole/3-wire
Receptacle Type	Single