

For abrasive materials, "professional" quality class







- Best suited for use on soft, abrasive materials such as fresh concrete, sand-lime brick, sandstone.
- Segment height: 5.0 mm
- For drilling without impact
- M16 female thread



Diameter mm	Segment height mm	Packing unit	Order No.
68	5	1	6.28203
82	5	1	6.28204

INTEGRAL CHUCKS FOR ROTARY HAMMERS

Hammer chucks with adapter

	Order No.
 <p>SDS-plus hammer chuck ■ For accessories with SDS-plus shank end (UHE 22, UHE 28 Multi, BHE 24, BHE 26, KHE 26 Contact, KHE 28)</p>	6.31920*
 <p>SDS-plus hammer chuck ■ For tools with SDS-plus shank end (for KHE 32)</p>	6.31922*
 <p>SDS-plus hammer chuck ■ For tools with SDS-plus shank end (UHE 2250/2650/ KHE 2650/2850/2851)</p>	6.31928*
 <p>SDS-plus hammer chuck ■ For tools with SDS-plus shank end (UHE 28 Plus, KHE 28 Plus)</p>	6.31931*

Chucks with adapter

	Order No.
 <p>Geared chuck with adapter ■ For accessories with cylindrical shank end (for UHE 22, UHE 28 Multi, BHE 24, BHE 26, KHE 26 Contact, KHE 28) Drill chuck clamping range 1 - 13 mm</p>	6.31924*
 <p>Quick-action keyless chuck with adapter ■ For accessories with cylindrical shank end (UHE 22, UHE 28 Multi, BHE 24, BHE 26, KHE 26 Contact, KHE 28) Drill chuck clamping range: 1.5 - 13 mm</p>	6.31921*
 <p>Quick-action keyless chuck with adapter ■ For tools with cylindrical shaft ■ Suitable for UHE 28 Plus/KHE 28 Plus Drill chuck clamping range: 1.5 - 13 mm</p>	6.31930*
 <p>Quick-action keyless chuck with adapter ■ For accessories with cylindrical shank end (for KHE 32) Drill chuck clamping range 1 - 13 mm</p>	6.31923*
 <p>Quick-action keyless chuck with adapter ■ For tools with cylindrical shaft ■ Suitable for: UHE 2250/2650/ KHE 2650/2850/2851 Drill chuck clamping range: 1.5 - 13 mm</p>	6.31927*

* Self-service packaging