

ENCLOSED HOSE REELS FOR COMPRESSED AIR / STAINLESS STEEL

DRFB/I Serie - Hose reel w/ safety retraction - Stainless steel -
Polyurethane hose Ether base



Part number	Length (m)	Flow rate (l/min)	Temperature min/ max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Profile
DRFINB 1012ESHE	12.00	800.00	-15.00 / 65.00	12.00	7,14	EUROPEAN

Part number	Dim. A (mm)	Dim. B (mm)	Ø int/ext (mm)
DRFINB 1012ESHE	370.00	337.00	10.00 / 14.00