

Angle Grinder XGT® 125mm

GA023G

40V max • 125 mm • 3 000 – 8 500 min⁻¹

Efficient brushless tool with brake for cutting and grinding

Brushless, slide switch angle grinder with a 125 mm wheel for demanding professional use. Adjustable speed from 3 000 – 8 500 min⁻¹ by using variable speed control dial. AWS remote vacuum cleaner start function.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	3000 - 8500 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	125 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,0 - 5,3 kg
Product Dimensions (L x W x H):	425 x 140 x 168 mm

User benefits

- Outperforming performance and efficiency similar to corded 1 000 W class grinder
- High durability; The upsized ball bearings support the rotor to withstand the high power of XGT tool
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor
- Slide switch with lock-on for continuous use
- Anti-restart function minimises accidental start-up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low
- Soft start for smooth start-ups

Link to product - www.makitauk.com



Related products

Optional AC

158237-4

Grip 36 complete



191G06-2

Dust collecting cover set



199710-5

Wheel Guard Cover 125 mm



782423-1

Lock nut wrench 35



821552-6

Makpac case (4)



Other

User manual

Parts drawing