

# Datasheet

## LED Rechargeable Task Light Kit



### Description

This LED rechargeable task light is suitable for both domestic and commercial tasks, especially in areas where there is no power. Supplied with both floor stand and tripod in a durable carry case, this task light is also cool to run and eliminates fire and burn hazards associated with halogen site lighting.

### Features

- 2-3 hours work time
- 2-3 hours charge time
- 10W LED chip
- Includes AC and in car charger
- Supplied with floor stand and tripod
- Durable foam lined carry case
- Daylight (6000K) colour temperature

### Range

LED Rechargeable Task Light Kit 7884612

### Dimensions (mm)

	Height	Width	Depth
7884612 (on stand)	240	150	170

### Technical Specification

Charger Input	230V AC or 12-24V DC
Charger Output	8.4V DC
Lamp Type	COB LED
Wattage	10W
Light Output	540lm
Lamp Col. Temp	6000K
IP Rating	IP65
Body Material	Die cast aluminium
Stand/Tripod Material	Steel

### Standards

- BS EN 60598-1: 2008+A11: 2009
- BS EN 60598-2-4: 1997
- BS EN 62493: 2010
- BS EN 62471: 2009