



Hand protection

EOS NOCUT VV910

LONG-LASTING CUT WORK

Level D cut, impact-resistant glove, ideal for multipurpose work in aqueous or oily environments



Specific benefits



Durability

• Longer service life thanks to a double coating for excellent abrasion resistance



Easy to use

• Perfect fit so that users do not feel any discomfort in the wrist area with prolonged use
• Hook-and-loop fastener for better wrist support



Hygiene

• Silicone-free/ DMF-free, leaving no residue on components while limiting allergies
• DMF-free to reduce the risk of allergies
• Washable glove, so it can be reused

Certifications and norms



EN 388

4 X 4 3 D P



EN 407

X 1 X X X X

ANSI ISEA 105

A4

Technologies & labels



DMF-free



Silicon-free

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Maintenance
- Chemical industry
- Automotive

Protects against risks



Shock



Cutting



Wearing



Perforation



Hand protection

EOS NOCUT VV910

LONG-LASTING CUT WORK

Level D cut, impact-resistant glove, ideal for multipurpose work in aqueous or oily environments

Standards - Details



EN388:2016+A1:2018

4 [0-4] ABRASION RESISTANCE
X [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
3 [0-4] PIERCE RESISTANCE
D [A-F] CUT RESISTANCE ISO 13997
P [P] IMPACT RESISTANCE (OPTIONAL)

Technical details

Glove kind	Special glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Special gloves kind	Impact
Coating material and finition	Nitrile double layer
Coating level	Palm coated
Number of layer	Double Layer
Gauge	13
Cuff characteristic	Velcro cuff
Benefits element	Reach, Silicone free, DMF free, Washable, Vendor pack, Azo Free
Color	Yellow-Grey-Black
Size	8, 9, 10, 11, 12
Type of packaging	Header card

Product care

- Flat drying



Safety gloves

EOS NOCUT VV910

LONG-LASTING CUT WORK

Level D cut, impact-resistant glove, ideal for multipurpose work in aqueous or oily environments

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VV910JA08	Yellow-Grey-Black	08	EOS NOCUT VV910	3295249191542	13295249191549	60	12	14.1 kg	70.0 cm	32.0 cm	23.0 cm
VV910JA09	Yellow-Grey-Black	09	EOS NOCUT VV910	3295249191559	13295249191556	60	12	13.394 kg	32.4 cm	70.4 cm	25.0 cm
VV910JA10	Yellow-Grey-Black	10	EOS NOCUT VV910	3295249191566	13295249191563	60	12	16.1 kg	34.6 cm	75.4 cm	29.8 cm
VV910JA11	Yellow-Grey-Black	11	EOS NOCUT VV910	3295249191573	13295249191570	60	12	13.6 kg	33.6 cm	72.6 cm	24.2 cm
VV910JA12	Yellow-Grey-Black	12	EOS NOCUT VV910	3295249302351	13295249302358	60	12	18.51 kg	36.8 cm	78.8 cm	28.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height