

## Features

- Imperial and Metric Sets
- Quick-release reversible ratched and accessories
- Durable PP co-polymer injection moulded case
- EVA high density foam inserts

## RS PRO 60 Piece 1/4" Drive Imperial/Metric Socket Set

RS Stock No.: 224-2248



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

A high-quality 60-piece socket set containing both Imperial and Metric socket sizes that can be used with any 1/4-inch drive ratchet.

The set includes:

- Regular and deep 6-point and 12-point sockets
- Slotted, Phillips Pozidriv, Torx and Hex bits, as well as Hex L keys

Accessories include:

- Quick release reversible ratchet
- Bit hold socket
- 2 x extension bars
- Spinner handle
- Universal joint
- Sliding T-Handle

## General Specifications

Set Type	Non-Impact Socket Set
Drive Type	Square
Number of Pieces	60
Set Contents	Quick release reversible ratchet; bit holder socket; 50mm extension bar; 150mm extension bar; 150mm spinner handle; universal joint; 115mm sliding t-handle; 6-point socket x11; 12-point socket x9; 6-point deep socket x6; 12-point deep socket x6; slotted bit x3; Phillips bit x2; pozidriv x2; torx x6; hex bit x4; hex l key x4
Finish	Polished Chrome
Material	Chrome Vanadium
Socket Product Type	6 point (mm); 6 point deep (mm); 12 point (in); 12 point deep (in)
Resistant Type	Corrosion-Resistant
Case Material	Polypropylene copolymer (PPC)
Carry Case/Bag Included	Yes

## Mechanical Specifications

Drive Size	1/4 inch
Socket Size	<p>12-POINT SOCKET (in): 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2</p> <p>6-POINT SOCKET (mm): 4, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13</p> <p>12-POINT DEEP SOCKET (in): 3/16, 1/4, 5/16, 3/8, 7/16, 1/2</p> <p>6-POINT DEEP SOCKET (mm): 6, 7, 8, 10, 12, 13</p> <p>SLOTTED BIT (mm): 4x25, 5.5x25, 6.5x25</p> <p>PHILLIPS BIT (mm): PH1x25, PH2x25</p> <p>POZIDRIV BIT (mm): PZ1x25, PZ2x25</p> <p>TORX BIT (mm): T10x25, T15x25, T20x25, T25x25, T30x25, T40x25</p> <p>HEXAGON BIT (mm): 3x25, 4x25, 5x25, 6x25</p> <p>HEXAGON L KEY / SHORT ARM (mm): 1.5, 2, 2.5, 3</p>
Net Weight	1.5 kg

## Approvals

Compliance/Certifications	DIN 3122, DIN 3123, DIN 3124
VDE/1000V Approved	No
Declarations	n/a