

Eaton 100LR85

Catalog Number: 100LR85

Eaton Bussmann series low voltage british standard fuse, 100A, AC 415 V, system C type II, 30 x 57 mm, gL/gG

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage british standard fuse	100LR85
	EAN
	5027590427807
Product Length/Depth	Product Height
57 mm	30.2 mm
Product Width	Product Weight
30.2 mm	101 g
Compliances	Certifications
CE Marked	BS
RoHS Compliant	IEC 60269



Electrical data

Amperage Rating

100 A

Voltage rating

415 V

Voltage type

AC

Breaking capacity

33 kA

Class

Class gG/gL

Product specifications

Application

protection of incoming cables into residential and commercial properties

Fuse type

LR85

Connection

Ferrule end x ferrule end

Resources

Catalogs

[CA134002EN](#)

Declarations of conformity

[CE KR85, LR85](#)

[UKCA KR85, LR85](#)

Multimedia

[Eaton Bussmann - Red Spot fuse links](#)

Technical data sheets

[720114 House service cut-out LR85 and KR85 fuses and fuse holders](#)

Technical service bulletins

[Datasheet - 100LR85](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia