

## eco!Booster TR 033

eco!Booster with 50% higher area performance than the Kärcher power nozzle for cold and hot water high-pressure cleaners (nozzle size 033); ideal for delicate surfaces.



Order no. **2.113-085.0**

### Technical data

EAN code		4066529118820
Pressure	bar	max. 300
Temperature	°C	max. 85
Nozzle size		33
Connection thread		EASY!Lock
Weight incl. packaging	kg	0.5



## 50% higher cleaning performance compared to the flat jet

- Thorough, fast and more sustainable cleaning.

## 50% higher water efficiency\*

- Saves water.
- \* Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

## 50% higher energy efficiency\*

- Saves energy.
- \* Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

## COMPATIBLE MACHINES

- HD 1.8/13 C Ed
- HD 6/15 M
- HDS 1.7/12 U Ed
- HDS 5/13 U