

SIMATIC HMI connecting cable for KTPX00(F) Mobile, length 10 m



Figure similar

| Standards, approvals, certificates                |        |
|---|--------|
| CE mark   | Yes    |
| cULus   | Yes    |
| RCM (formerly C-TICK)                             | Yes    |
| KC approval                                       | Yes    |
| Suitable for safety functions                     | Yes    |
| Ambient conditions                                |        |
| Ambient temperature during operation              |        |
| • min.  | 0 °C   |
| • max.  | 55 °C  |
| Ambient temperature during storage/transportation |        |
| • min.  | -20 °C |
| • max.  | 60 °C  |
| Cables  |        |
| Cable length                                      | 10 m   |
| Maximum tensile load                              | 300 N  |

|   |  |
|---|--|
| Color of cable sheath                   |  |
| • green                                 | Yes  |
| <b>Scope of supply</b>                  |  |
| Delivery quantity in pieces             | 1  |
| <b>Other</b>                            |  |
| Merchandise                             | Yes  |
| Manufacturer name                       | SIEMENS AG                                     |
| Manufacturer's address                  | Gleiwitzerstraße 555, 90475 Nuremberg, Germany |
| <b>Usable in the following products</b> |  |
| • Product 1                             | 6AV2125-2*                                     |
| • Product 2                             | 6AV2145-*                                      |
| • Product 3                             | 6AV2125-2DB23*                                 |
| <b>last modified:</b>                   | 04/10/2020                                     |