



DX4 HI-VIS DETACHABLE HOLSTER POCKET TROUSERS

DESCRIPTION

The DX4 Detachable Hi-Vis Holster Trousers are ergonomically designed and use the targeted placement of dynamic 4X stretch fabrics to give maximum range of movement when working. The trousers feature a high-rise back waistband with side elastics, ensuring protection in all working positions. Pre-bent top loading adjustable knee pad pockets, generously sized front pockets and multi-functional zip thigh pockets offer secure storage. Triple stitching throughout for maximum durability.

COMPOSITION

-  **Titanmill Pro Stretch: 92% Polyester, 8% Elastane, 235g**
-  **93% Polyester, 7% Elastane, 230g**
-  **CorePro: 88% Nylon 12% Elastane 245g**
-  **Yellow/Black 28-48**

FEATURES

- Texpel™ Stain Eco a premium stain resistant finish to repel grime and water
- 4-way stretch fabric for ease of movement and added comfort
- Stretch crotch gusset provides maximum flexibility and reduces stress
- Triple-stitched seams for extra durability
- Adjustable hem - regular to long leg
- Multiple utility pockets providing ample storage
- Reinforced side entry pockets
- 2 side zip pockets for secure storage
- 2 side zip cargo pockets
- Large back zip pocket for multiple storage options
- Rule pocket
- Hammer loop for secure storage of work tools

STANDARDS

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
DX442YBR	YELLOW/BLACK	28-14

FEATURES



HOLSTER POCKETS

This symbol indicates the trousers have swing away tool pockets.



TWO TIER KNEE PAD POCKETS

Two tier knee pad pockets allowing two positioning options



HEAT APPLIED SEGMENTED REFLECTIVE TAPE

This symbol indicates that the garment has heat applied reflective tape



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements



DX4™

DYNAMIC
4X
STRETCH

DYNAMIC 4X STRETCH

What defines this collection is its cutting edge slim fit design, high performance stretch fabrics and clever innovations ensure the wearer achieves maximum function, comfort and style.

GET THE COLLECTION



TECHINCAL INFORMATION



SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777) Bracetown
Business Park Clonée Dublin 15 D15 YN2P, Ireland
Cert No: 2777/20353-02/E00-00

- Wash garment inside out and fully fastened
- Wash dark colours separately

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
DX442YBR28	Yellow/Black	65	45	36	1.150	5850.000	5036108336838	15036108825223
DX442YBR30	Yellow/Black	65	45	36	1.180	5850.000	5036108336845	15036108825230
DX442YBR32	Yellow/Black	65	45	36	1.180	5850.000	5036108336852	15036108825247
DX442YBR33	Yellow/Black	65	45	36	1.140	5850.000	5036108336869	15036108825254
DX442YBR34	Yellow/Black	65	45	36	1.190	5850.000	5036108336876	15036108825261
DX442YBR36	Yellow/Black	65	45	36	1.170	5850.000	5036108336883	15036108825278
DX442YBR38	Yellow/Black	65	45	36	1.190	5850.000	5036108336890	15036108825285
DX442YBR40	Yellow/Black	65	45	36	1.200	5850.000	5036108336906	15036108825292
DX442YBR41	Yellow/Black	65	45	36	1.180	5850.000	5036108336913	15036108825308
DX442YBR42	Yellow/Black	65	45	36	1.220	5850.000	5036108336920	15036108825315
DX442YBR44	Yellow/Black	65	45	36	1.220	5850.000	5036108336937	15036108825322
DX442YBR46	Yellow/Black	65	45	36	1.250	5850.000	5036108336944	15036108825339
DX442YBR48	Yellow/Black	65	45	36	1.230	5850.000	5036108336951	15036108825346