



**Part Number :** [1200845182](#)  
**Product Description :** Ultra-Lock (M12)  
Receptacle, 12 Poles, Male, M16x1.5 Mounting  
Threads, PCB Pins, 5.00mm stand-off  
**Series Number :** 120084  
**Status :** Active  
**Product Category :** Circular Industrial  
Connectors  
**Engineering Number :** WRCW460003



---

## Documents & Resources

**Drawings**  
[1200845182\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	120084
Description	Ultra-Lock (M12) Receptacle, 12 Poles, Male, M16x1.5 Mounting Threads, PCB Pins, 5.00mm stand-off
IP Rating	IP69K
NEMA Rating	NEMA 6
Product Name	Ultra-Lock (M12)
Type	PCB Mount
UPC	78172538865

### Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V AC/DC

### Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Net Weight	21.568/g
Orientation	Straight
Panel Mount	Back
Poles	12
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

---

---

This document was generated on Mar 27, 2025