



Main

Range of product	IC60 Reflex iC60
Device short name	Vigi iC60
Poles description	4P
Network type	AC

Complementary

Device location in system	Outgoer
[In] rated current	63 A
Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V EN 61009-1 AC 50/60 Hz 400/415 V IEC 61009-1 AC 50/60 Hz
Overvoltage protection	Without
Residual current tripping technology	Voltage independent
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Class AC
Local signalling	Trip indicator
Mounting mode	Removable comb busbar installed
Mounting support	DIN rail
Electrical connection to mcb	By screws
9 mm pitches	7
Width	135 mm
Connections - terminals	Tunnel terminal with flap downside

Environment

Standards	EN 61009-1 IEC 61009-1
RoHS EUR status	Compliant
RoHS EUR conformity date	1001