

CES-SRG-BK-2X7 - Cable sleeve



1410084

<https://www.phoenixcontact.com/gb/products/1410084>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 6 mm ... 7 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

Product description

Slotted cable sleeve

Commercial data

Item number	1410084
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7CCX
Product key	AF7CCX
Catalog page	Page 679 (C-2-2019)
GTIN	4046356776325
Weight per piece (including packing)	7.38 g
Weight per piece (excluding packing)	7 g
Customs tariff number	40169997
Country of origin	TW

CES-SRG-BK-2X7 - Cable sleeve

1410084


<https://www.phoenixcontact.com/gb/products/1410084>

Technical data

Product properties

Product type	Cable sleeve
No. of conductors	2

Dimensions

Dimensional drawing	
Width	19.5 mm
Height	17 mm
Length	29.5 mm

Material specifications

Material	NBR
----------	-----

Cable/line

External cable diameter	2x 6 mm ... 7 mm
-------------------------	------------------

Characteristics

Seal size	small
Design, Format	Round cable
Design, Cable seal	slotted

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C (static)

CES-SRG-BK-2X7 - Cable sleeve


1410084

<https://www.phoenixcontact.com/gb/products/1410084>



Drawings

Dimensional drawing



Dimensional drawing

CES-SRG-BK-2X7 - Cable sleeve



1410084

<https://www.phoenixcontact.com/gb/products/1410084>

Classifications

ECLASS

ECLASS-13.0	27144425
-------------	----------

ETIM

ETIM 9.0	EC000451
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CES-SRG-BK-2X7 - Cable sleeve



1410084

<https://www.phoenixcontact.com/gb/products/1410084>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.582 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk