

Technical data sheet

Article number:
924-00439

QDF2-5F/8

Product Group	Quick Connect Fully Insulated Female Funnel Entry
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyvinylchloride (PVC), Copper (CU)
Colour	Blue (BU)
Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm ²
Diameter (D)	4.9 mm
Halogen-free	No
Length (L)	21 mm
Length (L2)	11.5 mm
Max Current	15 A
Max Voltage	300 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	7.8 mm
Width (W2)	5 mm

RoHS 