

LONG LIFE CUTTING METAL

PRO

- 1 Robust aluminium oxide grains for long-lasting performance
- 2 Resin matrix for strength and resistance to heat
- 3 Strong fibreglass net reinforces the disc



Video



BOSCH

PRO METAL BONDED CUTTING DISC

PRO


- ▶ For cutting metal in general metalworking applications
- ▶ Highly efficient for metalworkers: Long Life
- ▶ Designed for cutting metal
- ▶ With 22.23 mm bore for standard locking nut angle grinders



PRODUCT PROPERTIES							ORDERING INFORMATION				
Specification	Diameter mm	Bore diameter mm	Thickness mm	X-LOCK	oSa	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number	
AS 46 S BF	115	22.23	1.6	-	●	U0	1	25	116 350	2 608 600 214	
A 60 T BF	115	22.23	1.6	-	-	U0	1	25	658 607	2 608 603 163	
With depressed centre											
A 30 S BF	115	22.23	2.5	-	●	U0	1	25	031 196	2 608 600 005	
Straight											
A 30 S BF	115	22.23	2.5	-	●	U0	1	25	149 402	2 608 600 318	
With depressed centre											
A 30 S BF	115	22.23	2.5	-	-	U0	1	25	658 560	2 608 603 159	
Straight											
A 30 S BF	115	22.23	2.5	-	-	U0	1	25	658 614	2 608 603 164	
With depressed centre											
A 30 S BF	115	22.23	3.0	-	●	U0	1	25	863 919	2 608 601 567	
Straight											
A 30 S BF	115	22.23	3.0	-	●	U0	1	25	706 872	2 608 603 395	
AS 46 S BF	125	22.23	1.6	-	●	U0	1	25	116 404	2 608 600 219	
A 60 T BF	125	22.23	1.6	-	-	U0	1	25	658 249	2 608 603 165	
With depressed centre											
A 30 S BF	125	22.23	2.5	-	●	U0	1	25	116 428	2 608 600 221	
Straight											
A 30 S BF	125	22.23	2.5	-	●	U0	1	25	181 846	2 608 600 394	
With depressed centre											
A 30 S BF	125	22.23	2.5	-	-	U0	1	25	658 577	2 608 603 160	
Straight											
A 30 S BF	125	22.23	2.5	-	-	U0	1	25	658 256	2 608 603 166	
A 30 S BF	150	22.23	2.5	-	●	U0	1	25	181 716	2 608 600 382	
A 30 S BF	150	22.23	2.5	-	-	U0	1	25	631 417	2 608 619 774	


BOSCH