

SIMATIC IPC MD-34A 2-bay battery charger; you must select your power supply cord; EU: 6ES7900-5AA00-0XA0 GB: 6ES7900-5BA00-0XA0 Swiss: 6ES7900-5CA00-0XA0 USA: 6ES7900-5DA00-0XA0 Italy: 6ES7900-5EA00-0XA0 China: 6ES7900-5FA00-0XA0 India: 6ES7900-5GA00-0XA0



General information			
Design of the programming device	Mobile computer		
Supply voltage			
Rated value (DC)	19 V		
permissible range, lower limit (AC)	100 V		
permissible range, upper limit (AC)	240 V		
Standards, approvals, certificates			
CE mark	Yes		
Ambient conditions			
Ambient temperature during operation			
• min.	0 °C		
• max.	45 °C		
Ambient temperature during storage/transportation			
• min.	-20 °C		
• max.	60 °C		
Relative humidity			
• Operation, min.	50 %		
• Operation, max.	95 %		
Dimensions			
Width	216 mm		
Height	81 mm		
Depth	50 mm		
Weights			
Weight, approx.	340 mg		
Classifications			
		Version	Classification
	eClass	14	27-33-02-92
	eClass	12	27-33-02-92
	eClass	9.1	27-33-02-92
	eClass	9	27-33-02-92
	eClass	8	27-24-92-03
	eClass	7.1	27-24-92-03
	eClass	6	27-24-92-03
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584



[China RoHS](#)



last modified:

5/17/2025 