

# ROBUST SCREWDRIVING

## PRO

- 1 Extended torsion zone absorbs the torque stress at the bit's tip
- 2 Heat-treated modified steel for strength and resistance to high torque



\* vs Bosch 2607001528

## PRO IMPACT PZ SCREWDRIVER BIT

**PRO**


- ▶ For driving PZ screws efficiently, eg when installing all types of panels, equipment, and fixtures
- ▶ Highly efficient for installers, electricians, metalworkers, and woodworkers: Robust
- ▶ Up to 50x more robust than a Bosch 2607001528 Extra Hard Bit
- ▶ 1/4" Impact rated Hex shank for use in impact driver and drill driver



PRODUCT PROPERTIES	ORDERING INFORMATION				
	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number
PZ1, 25 mm, 2 pcs	PC1d	2	5	919 982	2 608 522 400
PZ2, 25 mm, 2 pcs	PC1d	2	5	919 999	2 608 522 401
PZ3, 25 mm, 2 pcs	PC1d	2	5	920 001	2 608 522 402
PZ1; PZ2; PZ3, 25 mm, 3 pcs	PC1d	3	5	233 363	2 608 522 471
PZ2, 25 mm, 8 pcs, with Pick and Click Index	PC1a	8	5	851 152	2 608 522 325
PZ2, 25 mm, 10 x 25 pcs, <b>with Display</b>	P1a	25	10	980 234	2 607 002 804
PZ1, 55 mm, 2 pcs	PC1d	2	5	242 150	2 608 522 543
PZ2, 55 mm, 2 pcs	PC1d	2	5	242 167	2 608 522 544
PZ3, 55 mm, 2 pcs	PC1d	2	5	242 174	2 608 522 545
PZ1; PZ2; PZ3, 55 mm, 3 pcs	PC1d	3	5	242 181	2 608 521 U57
PZ2, 55 mm, 8 pcs, with Pick and Click Index	PC1a	8	5	851 213	2 608 522 331
PZ2, 55 mm, 15 pcs, <b>with Display</b>	P1k	15	10	242 198	2 608 522 546
PZ2, 90 mm	PC1d	1	5	242 204	2 608 522 547
PZ2, 150 mm	PC1d	1	5	242 211	2 608 522 548


**BOSCH**