

Datasheet

RS Line Mounting Hydraulic Flow Control Valve, G 1/8

RS Stock number 390-7667



MATERIALS

- **Body** 9 S Mn Pb 23 - UNI 5105
- **Needle** 1 C 40 - UNI 8373
- **OR** nitrile
- **Antiextrusion ring** PTFE
- **Handwheel** GD - Al Si 12 - UNI 5706
aluminium
- **Handwheel (mp)** ABS - plastic

In line double-acting flow control and shut-off control needle valves

They allow flow control in both directions. Needle adjustments give:

- full shut off (via metal seat);
- accurate control for a wide range of flowrates.

The valve has a graduated adjustment scale below the handle to indicate accurately the valve position.

There is a locking screw in the handle to allow the handle to be fixed.

(Preventing accidental adjustment or movement due to vibration).

A panel mounting nut (G) can be supplied on request.

On request

- Versions in AISI 316 stainless steel code FT 2257/2
- Viton seals (V)
- NPT threads
- Complete with panel mounting nut (G)
- Handwheel in ABS (mp) - plastic