

Datasheet

RS Pro Sling Point Steel Zinc Plated, Side Mounted

RS Stock No: **379-9292**



Product Details

RS Pro sling point has a side mounted mount style with zinc plated finish. It is made from stainless steel and fixed to the side of containers as a sling point for lifting.

Features and Benefits

- Fixed to the side of containers as a sling point for lifting
- Ring is kept flat against the container when not in use by means of a leaf spring
- Leaf spring also keeps the ring extended at 90° to the container wall when in use
- Particularly useful when attaching several hooks to slings positioned around the container



ENGLISH

Specifications:

Finish	Zinc Plated
Load Capacity	70 kg
Load Plate Dimensions	60.5 x 124 mm
Load Plate Width	124 mm
Material	Steel
Mount Style	Side Mounted
Plate Length	60.5 mm