



Datasheet

EN

RS Pro SW-608RS 8 Port Hardened Ethernet Switch

Stock Number: 144-8676



Specifications:

- Power Consumption: 1.5 Watts Max : 300 mAmps@+5VDC/50mAmps@+30VDC
- Power Supply input: Unregulated +5V to +30Volts DC, reverse polarity protection
- Operating Temperature: -40°C to +80°C/-40°F to +176°F
- Ethernet Ports: 8 x RJ45 jack, 10/100Mhz autosensing, crossover auto sensing (Auto MDIX)
- Unmanaged 10/100Mbps Ethernet
- Housing: IP-20 rated metal case with Easy Wire Removable screw terminal block
- Weight: 0.37 kg
- Dimensions: 115x99x41 mm

Features:

- 8 Port 10/100 Mbs Ethernet Switch
- Redundant dual power inputs: +5V to +30V DC
- Compact design with integral DIN mount
- No software required - Simply plug in and connect
- Industrial temperature range

