



Magigoo Original, PA, PC, Flex, Metal, HT

ACCORDING TO EC-REGULATIONS 1907/2006 (REACH), 1272/2008 (CLP) & 2015/830

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifier

Product Name	Magigoo Original, PA, PC, Flex, HT, Metal
CAS No.	Not applicable.
EC No.	Not applicable.
REACH Registration No.	Not known.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified Use(s)	3D Printing
Uses Advised Against	Not known.

1.3 Details of the supplier of the safety data sheet

Manufacturer

Company Identification	Thought3D
Address of Manufacturer	Thought3D KBIC Unit 2150, Kordin industrial Estate
Postal code	PLA3000
Telephone:	99587397
Fax	Not known.
E-mail	info@thought3d.com
Office hours	

Supplier

Company Identification	Thought3D
Address of Supplier	Thought3D KBIC Unit 2150, Kordin industrial Estate
Postal code	PLA3000
Telephone:	99587397
E-mail	info@thought3d.com
Office hours	

1.4 Emergency telephone number

Emergency Phone No.	Not known.
Contact	No information available.

SECTION 2: HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Regulation (EC) No. 1272/2008 (CLP)	Not classified as dangerous for supply/use.
-------------------------------------	---

2.2 Label elements

	According to Regulation (EC) No. 1272/2008 (CLP)
Product Names	Magigoo Original, PA, PP, PC, Flex, Metal, HT



Magigoo Original, PA, PC, Flex, Metal, HT

Hazard Pictogram(s) None.

Signal Word(s) None.

Hazard Statement(s) None.

Precautionary Statement(s) None.

2.3 Other hazards

None known.

2.4 Additional Information

None.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Not applicable.

3.2 Mixtures

The product does not contain dangerous substances

SECTION 4: FIRST AID MEASURES

4.1 Description of first aid measures

Inhalation	If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.
Skin Contact	Wash skin with water.
Eye Contact	Flush eyes with water for at least 15 minutes.
Ingestion	Wash out mouth with water.

4.2 Most important symptoms and effects, both acute and delayed

None anticipated. Treat symptomatically.

4.3 Indication of any immediate medical attention and special treatment needed

Unlikely to be required but if necessary treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable Extinguishing media	As appropriate for surrounding fire.
Unsuitable extinguishing media	None.

5.2 Special hazards arising from the substance or mixture

None anticipated. Heating may cause decomposition.

5.3 Advice for firefighters

As appropriate for surrounding fire.



Magigoo Original, PA, PC, Flex, Metal, HT

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Provide adequate ventilation. Wear suitable gloves if prolonged skin contact is likely.

6.2 Environmental precautions

Do not release large quantities into the surface water or into drains.

6.3 Methods and material for containment and cleaning up

Adsorb spillages onto sand, earth or any suitable adsorbent material.

6.4 Reference to other sections

See Also Section 8, 13.

SECTION 7: HANDLING AND STORAGE

7.1 Precautions for safe handling

Not known.

7.2 Conditions for safe storage, including any incompatibilities

Storage temperature	Ambient.
Storage life	Stable under normal conditions.
Incompatible materials	None known.

7.3 Specific end use(s)

Not known.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

8.1.1 Occupational Exposure Limits No Occupational Exposure Limit assigned.

8.2 Exposure controls

8.2.1. Appropriate engineering controls Ensure adequate ventilation.

8.2.2. Personal protection equipment



Eye Protection Wear eye protection with side protection (EN166).



Skin protection Not normally required.



Respiratory protection Normally no personal respiratory protection is necessary.



Magigoo Original, PA, PC, Flex, Metal, HT



Thermal hazards None known.

8.2.3. Environmental Exposure Controls Do not release large quantities into the surface water or into drains.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance	Liquid. Colour : Almost colourless to pale yellow.
Odour	Almost odourless.
Odour threshold	Not known.
pH	4-7.
Melting point/freezing point	Not known.
Initial boiling point and boiling range	Not known.
Flash Point	Not known.
Evaporation rate	Not known.
Flammability (solid, gas)	Not known.
Upper/lower flammability or explosive limits	Not known.
Vapour pressure	Not known.
Vapour density	Not known.
Density (g/ml)	Not known.
Relative density	Not known.
Solubility(ies)	Solubility (Water) : Completely miscible with water. Solubility (Other) : Not known.
Partition coefficient: n-octanol/water	Not known.
Auto-ignition temperature	Not known.
Decomposition Temperature (° C)	Not known.
Viscosity	
Explosive properties	Not known.
Oxidising properties	Not known.

9.2 Other information

SECTION 10: STABILITY AND REACTIVITY

10.1 Reactivity

None anticipated.

10.2 Chemical Stability

Stable under normal conditions.



Magigoo Original, PA, PC, Flex, Metal, HT

10.3 Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose.

10.4 Conditions to avoid

None anticipated.

10.5 Incompatible materials

Not known.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity - Ingestion	Low acute toxicity
Acute toxicity - Skin Contact	Low acute toxicity
Acute toxicity - Inhalation	Low acute toxicity
Skin corrosion/irritation	Non-irritant
Serious eye damage/irritation	Non-irritant
Skin sensitization data	Not classified
Respiratory sensitization data	Not classified
Germ cell mutagenicity	There is no evidence of mutagenic potential.
Carcinogenicity	No evidence of carcinogenicity.
Reproductive toxicity	Not classified
Lactation	Not classified
STOT - single exposure	Not classified
STOT - repeated exposure	Not classified
Aspiration hazard	Not classified

11.2 Other information

Not known.

SECTION 12: ECOLOGICAL INFORMATION

12.1 Toxicity

Toxicity - Aquatic invertebrates	Low toxicity to invertebrates.
Toxicity - Fish	Low toxicity to fish.
Toxicity - Algae	Low toxicity to algae.
Toxicity - Sediment Compartment	Not classified.
Toxicity - Terrestrial Compartment	Not classified.

12.2 Persistence and Degradation

Not known.

12.3 Bioaccumulative potential

Not known.



Magigoo Original, PA, PC, Flex, Metal, HT

12.4 Mobility in soil

Not known.

12.5 Results of PBT and vPvB assessment

Not known.

12.6 Other adverse effects

Not known.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Dispose at suitable refuse site.

13.2 Additional Information

No special precautions are required for this product.

SECTION 14: TRANSPORT INFORMATION

Not classified as hazardous for transport.

14.1 UN number

Not applicable

14.2 UN proper shipping name

Not applicable

14.3 Transport hazard class(es)

Not applicable

14.4 Packing group

Not applicable

14.5 Environmental hazards

Not classified as a Marine Pollutant.

14.6 Special precautions for user

Not known

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not known

SECTION 15: REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

European Regulations - Authorisations and/or Restrictions On Use

Candidate List of Substances of Very High Concern for Authorisation Not listed

REACH: ANNEX XIV list of substances subject to authorisation Not listed

REACH: ANNEX XIV list of substances subject to authorisation Not listed



Magigoo Original, PA, PC, Flex, Metal, HT

REACH: Annex XVII Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles

Community Rolling Action Plan (CoRAP) Not listed

Regulation (EC) N° 850/2004 of the European Parliament and of the Council on persistent organic pollutants Not listed

Regulation (EC) N° 1005/2009 on substances that deplete the ozone layer Not listed

Regulation (EU) N° 649/2012 of the European Parliament and of the Council concerning the export and import of hazardous chemicals Not listed

National regulations

Other Not known.

15.2 Chemical Safety Assessment

A REACH chemical safety assessment has not been carried out.

SECTION 16: OTHER INFORMATION

The following sections contain revisions or new statements:

LEGEND

Hazard Pictogram(s) None.

Hazard Statement(s) None.

Precautionary Statement(s) None.

Acronyms

CAS : Chemical Abstracts Service

CLP : Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures

DNEL : Derived No Effect Level

EC : European Community

EINECS : European Inventory of Existing Commercial Chemical Substances

LTEL : Long term exposure limit

PBT : Persistent, Bioaccumulative and Toxic

PNEC : Predicted No Effect Concentration

REACH : Registration, Evaluation, Authorisation and Restriction of Chemicals

STEL : Short term exposure limit

STOT : Specific Target Organ Toxicity



Magigoo Original, PA, PC, Flex, Metal, HT

vPvB : very Persistent and very Bioaccumulative

Disclaimers

Information contained in this publication or as otherwise supplied to Users is believed to be accurate and is given in good faith, but it is for the Users to satisfy themselves of the suitability of the product for their own particular purpose. Thought3D gives no warranty as to the fitness of the product for any particular purpose and any implied warranty or condition (statutory or otherwise) is excluded except to the extent that exclusion is prevented by law. Thought3D accepts no liability for loss or damage (other than that arising from death or personal injury caused by defective product, if proved), resulting from reliance on this information. Freedom under Patents, Copyright and Designs cannot be assumed.